© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G2	REVISED PER ECR-25-255998	16SEP2025	SA	DSC



1 FOR .050 TO .080 WIRE INSULATION DIA.

2 BRAZED SEAM ON BUTT SPLICE BODY.

3 MATERIAL: INSULATION – PVC
COLOR – YELLOW, TRANSPARENT
BODY – COPPER PER ASTM B152
FINISH – TIN PL. PER ASTM B545

QTY	DESCRIPTION	PART NO
100	LOOSE PIECE	8-321026-1
1 KIT = 250 PIECES	LOOSE PIECE	6-321026-0
4000	ON TAPE	2-321026-1
1000	LOOSE PIECE	321026

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± .008
4 PLC ± –
ANGLES ± 5°

MATERIAL 3

FINISH 3

DWN jr ruth 27OCT04
CHK T MICHIELUTTI 27OCT04
APVD T MICHIELUTTI 27OCT04
PRODUCT SPEC —
APPLICATION SPEC 114-2161
WEIGHT —

TE Connectivity

NAME
WIRE BUTT SPLICE,
PLASTI-GRIP,
WIRE SIZE: 26-22 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-321026	—

CUSTOMER DRAWING

SCALE	SHEET	REV
1:1	1 OF 1	G2