


© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	PCN-25-266608	25MAY2026	GSK	CAS







RECOMMENDED PANEL CUTOUT

1. HOUSING, ADAPTER AND PRESSURE PLATE: THERMOPLASTIC, BLACK.
   WIRE ENTRY SEAL: ELASTOMER, RED-IRON OXIDE.
   PERIPHERAL SEAL: ELASTOMER, BLACK.
2. NUMBER 4 FASTENERS RECOMMENDED FOR MOUNTING.
3. CONNECTOR WILL ACCEPT (24) MULTIMATE PIN CONTACTS.

1.65-2.54[.065-.100]	796190-1
WIRE INSULATION DIAMETER RANGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± 0.13 [.005]
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL 1

FINISH –

DWN C.DORWART 16 JUL 98
CHK K.DOWHOWER 10 AUG 99
APVD K.DOWHOWER 10 AUG 99
PRODUCT SPEC 108-1579
APPLICATION SPEC –
WEIGHT

TE Connectivity

NAME
RECEPTACLE ASSEMBLY,
STANDARD SEX, SIZE 23-24,
SEALED CPC

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-796190	–

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV D

796190