

NUMBER 178139



3rd ANGLE PROJECTION

METRIC




DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

VIEW A
回路番号
CIRCUIT NO
AMPマーク
シリーズマーク
SERIES MARK




△ 4	△ 3	1,2,3,5,6-178139-5
△ 3	△ 2	1,2,3-178139-3
△ 2		1,2,3,4-178139-2
(FINISH)		製品番号 (PART NO.)



NOTES

- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- FINISH (CONTACT AREA): 0.38μm PdNi & Au PLATING OVER NICKEL
- FINISH (CONTACT AREA): 0.76μm PdNi & Au PLATING OVER NICKEL
- FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL
- FINISH (RETENTION LEG): TIN LEAD PLATED (CONTACT TAIL) OVER NICKEL
- PRODUCT SPEC: 108-5349
- FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL



推奨基板取付け寸法
PC 基板厚: 1.6±0.1
(非累積公差)
(コネクタ搭載面)

RECOMEND PC BOARD HOLE PATTERN
PC BOARD THICKNESS: 1.6±0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

								TE Connectivity			
								6 POS SINGLE ROW HORIZONTAL HDR ASS'Y FOR DYNAMIC D-3200			
								C-178139			
								F			
								1 OF 1			

(CUSTOMER DRAWING) 顧客用図面