


NUMBER 178325





METRIC

PRINT DIST DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

AMP-J
REV.10/'83



推奨基板取付け穴寸法
PC 基板厚: 1.6±0.1
(非累積公差)
(コネクタ搭載面)

RECOMEND PC BOARD HOLE PATTERN
PC BOARD THICKNESS: 1.6±0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

- NOTES
1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER (94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
 2. RETENTION LEG: COPPER ALLOY
 3. FINISH (CONTACT AREA): 0.38μm PdNi & Au PLATING OVER NICKEL
 4. FINISH (CONTACT AREA): 0.76μm PdNi & Au PLATING OVER NICKEL
 5. FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL
 6. FINISH (RETENTION LEG): TIN LEAD PLATED (CONTACT TAIL) OVER NICKEL
 7. FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL
 7. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE THEY DON'T SHOW DETAILS
 8. THE DATE CODE SHOW PRODUCTION LOT BY NUMBER. THE NUMBER MAKE UP THE NUMBER OF FOUR COLUMNS OR FIVE COLUMNS. (INCLUDE THE ALPHABET)

△6	△4	178325-5
△6	△3	178325-3
△6	△2	178325-2
(FINISH)		製品番号 (PART NO.)

G	REVISED PER ECR-25-250788	F.Z	R.B	16JAN 2025
LTR	REVISION RECORD	DR	CHK	DATE

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		TE Connectivity	
WIRE RANGE mm ² (AWG -)	INSULATION DIA mmφ	NAME 10 POS DOUBLE ROW VERTICAL HDR ASS'Y FOR DYNAMIC D-3100	
MATERIAL SEE NOTE 注記参照	FINISH SEE NOTE 注記参照	一般公差 (GENERAL TOLERANCE)	SIZE LOC NUMBER A3 J C-178325
DR. 19 APR 94 N. Matsubara	DE. 19 APR 94 N. Matsubara	10mm 30mm 10mm 30mm 10mm 30mm ±0.3 ±0.4 ±0.4 ±0.45 ±3	SCALE 2-1
CHK. S. MANABE	APP. S. MANABE	REV. G	SHEET 1 OF 1

(CUSTOMER DRAWING) 顧客用図面