

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	W1	REVISED PER ECN-22-165832	22JUL2022	RK	MZ

- 1

HOUSING: NYLON, BLACK.
PERIPHERAL SEAL: ELASTOMER, BLACK.
THREADED INSERTS: BRASS.
- 2




CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 3

WILL ACCEPT (16) MULTIMATE PIN CONTACTS.
- 4

HOUSING: NYLON, BLUE.
PERIPHERAL SEAL: ELASTOMER, BLACK.
THREADED INSERTS: BRASS.
- 5

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6

TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE






RECOMMENDED PANEL CUTOUT

5 OBSOLETE		STANDARD	ø3.81(.125) HOLES	YES	206036-9
		STANDARD	#4-40 THREADED INSERTS	NO	206036-8
		SMALL PACK	ø3.81(.125) HOLES	NO	206036-7
		STANDARD	ø3.81(.125) HOLES	YES	206036-4
		STANDARD	ø3.81(.125) HOLES	NO	206036-1
	MATERIAL		PACKAGING	MOUNTING FEATURES	PERIPHERAL SEAL

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN D. GELTZ CHK R. STONE	07/27/93 7-22-93	 TE Connectivity Ltd.					
DIMENSIONS: MM[INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		REV'D A. FRANTUM 8-12-93		NAME					
		1 P/LC ± -		PRODUCT SPEC		RECEPTACLE HOUSING, STD SEX, SHELL SIZE 17, CPC -					
		2 P/LC ± -		108-10024							
		3 P/LC ± 0.15 [.005]		APPLICATION SPEC							
4 P/LC ± -		ANGLE'S ± -		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
MATERIAL		FINISH		WEIGHT		A1		00779			206036
CUSTOMER DRAWING				SCALE		2:1		SHEET		1 OF 3	REV W

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

- 1 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 2 WILL ACCEPT (3) TYPE XII PIN CONTACTS.
- 3 HOUSING: NYLON, BLACK.
PERIPHERAL SEAL: ELASTOMER, BLACK.
- 4 TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE





RECOMMENDED PANEL CUTOUT

PRELIMINARY OBSOLETE	3	ø3.18(.125) HOLES	YES	1-206036-6
	3	#4-40 THREADED INSERTS	NO	1-206036-4
	3	ø3.18(.125) HOLES	NO	206036-2
MATERIAL		MOUNTING FEATURES	PERIPHERAL SEAL	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. GELTZ CHK R. STONE APVD A. FRANTUM	TE Connectivity Ltd.	
DIMENSIONS: MM(INCH)		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	
		0 PLC ± -	PRODUCT SPEC	
		1 PLC ± -	108-10024	
		2 PLC ± 0.13 [.005]	APPLICATION SPEC	
MATERIAL		FINISH	WEIGHT	RESTRICTED TO
-		-	-	-
CUSTOMER DRAWING		SCALE	SHEET	REV
		2:1	2 OF 3	W1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

- 1
- CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 2
- WILL ACCEPT (16) MULTIMATE PIN CONTACTS.
- 3
- HOUSING: NYLON, BLACK.
PERIPHERAL SEAL: ELASTOMER, BLACK.
- 4
- HOUSING: POLYESTER, PBT, BLACK.
PERIPHERAL SEAL: ELASTOMER, BLACK.
THREADED INSERTS: BRASS



OBSOLETE	4	NO	1-206036-3
	3	YES	206036-5
	3	NO	206036-3
MATERIAL		PERIPHERAL SEAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. GELTZ 07/27/93	 TE Connectivity Ltd.	
		CHK R. STONE 7-22-93		
DIMENSIONS: MM[INCH]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD A. FRANTUM 8-12-93	NAME	
		PRODUCT SPEC	RECEPTACLE HOUSING, STD SEX, SHELL SIZE 17, CPC	
	0. PLC ± - 1. PLC ± - 2. PLC ± 0.13 [.005] 3. PLC ± - 4. PLC ± - ANGLES ± -	APPLICATION SPEC	—	
		WEIGHT —	RESTRICTED TO	
MATERIAL —	FINISH —	WEIGHT —	A1 00779 C=206036 —	
CUSTOMER DRAWING		SCALE 2:1	SHEET 3 OF 3	REV W