














LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	INITIAL RELEASE	11MAR2025	J. J	H. L



△ MATERIALS AND FINISH:
 -HOUSING: LCP, COLOR: NATURAL
 -CONTACTS: COPPER ALLOY, FINISH: S_n OVER Ni
 -HOLD DOWNS: STAINLESS STEEL, FINISH: S_n OVER Ni

2. PACKAGED IN TAPE AND REEL PER EIA-481 SPECIFICATIONS.
DIAMETER OF REEL TO BE 330.0mm





2481779-2

2481779-4

2481779-5





5	2481779-5
4	2481779-4
2	2481779-2
POS	PART NUMBER



MINI-CT -
INTERFACE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JONE JJ 01FEB2024	 TE Connectivity					
		CHK HOPE LU 01FEB2024						
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME ASSEMBLY, MINI CT 1.5mm PITCH SMT TYPE -					
	0 PLC ±.35 1 PLC ±0.3 2 PLC ±.3 3 PLC ±. 4 PLC ±. ANGLES ±3° FINISH	PRODUCT SPEC 108-161342						
MATERIAL 		APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO -		
		WEIGHT -	A2	00779	C-2481779			
CUSTOMER DRAWING			SCALE	1:1	SHEET	1 OF 3	REV	A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		-	SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT
ODD NUMBER POSITIONS SHOWN
SCALE 10:1

15.70	10.5	5	2481779-5
14.20	9.00	4	2481779-4
11.20	6.00	2	2481779-2
DIM N	DIM M	POS	PART NUMBER


RECOMMENDED PCB LAYOUT
EVEN NUMBER POSITIONS SHOWN
SCALE 10:1

FOR REFERENCE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JONE JJ	01FEB2024		 TE Connectivity	
		CHK HOPE LU	01FEB2024			
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	-	NAME	ASSEMBLY, MINI CT 1.5mm PITCH SMT TYPE	
mm		PRODUCT SPEC				
	0 PLC ±. 1 PLC ±0.35 2 PLC ±0.3 3 PLC ±. 4 PLC ±.	APPLICATION SPEC	108-161342			
MATERIAL	ANGLES ±3° FINISH	-		SIZE	CAGE CODE	DRAWING NO
		WEIGHT -	A2	00779	G-2481779	RESTRICTED TO -
CUSTOMER DRAWING				SCALE	1:1	SHEET 2 OF 3 REV A


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		-	SEE SHEET 1	-	-	-

D




C

B



SECTION Z-Z

PACKAGE FOR REFERENCE



D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JONE JI CHK HOPE LU	01FEB2024 01FEB2024	TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± 1 PLC ±0.35 2 PLC ±0.3 3 PLC ± 4 PLC ± ANGLES ±3° FINISH		ASSEMBLY, MINI CT 1.5mm PITCH SMT TYPE			
MATERIAL		APVD PRODUCT SPEC 108-161342 APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C-2481779	RESTRICTED TO -
				SCALE 1:1	SHEET 3	OF 3	REV A

A