


THERMOFIT • SPECIFICATION CONTROL DRAWING • MOLDED PARTS

NOTES

- All dimensions are in inches; all angles are in degrees.
- Dimensions appearing in table below are as follows:
 a - As supplied b - After unrestricted recovery
- Weight shown in table of dimensions is based on polyolefin part.
- Molding ports are optional. When specified, they will be located as shown. Order 381A115-3-00 when molding ports are required.

If this document is printed it becomes uncontrolled.
 Check for the latest revision.



ORDERING
INFORMATION

Matl. No.	Description	Rayclad Matl. Spec.	Specific Grav. Max.
3	Polyolefin	RT 301	1.40
4	Flex poly	RT 1304	1.40
5	Neoprene	RT 501	1.50
6	Silicone, flame retarded	RT 602	1.35
12	Viton	RT 1312	1.95
25	Elastomer, fluid resistant	RT 1325	

Add material number as suffix to part number;
 Example - Order 381A115-3 when polyolefin is required.

TABLE OF DIMENSIONS

PART NO.	H		J and K		P		R		HW		JW and KW		C		Weight lbs ±10%		
	Min a	Max b	Min a	Max b	Max a	±10% b	Max a	±10% b	a	±20% b	a	±20% b	±10° a	±5° b			
381A115-	1.12	.49	1.06	.49	—	3.44	—	3.45	—	.10	—	.10	10	22-1/2	.135		

Raychem

E.O. REV DATE DESCRIPTION

DRN	DD
CHK'D	KT
AUTH	RW
AUTH	HP

PART DESCRIPTION
 TRANSITION, Y

PART NO.
 381A115

REV LTR
 D

DATE
 May 31, 1984