

AD 3 SAK6N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Similar to illustration

Warning covers with a flash symbol provide more safety for man and machine. They are used where external voltage must be indicated within the application.

General ordering data

Version	Terminal cover, yellow, PVC, Height: 25 mm, Width: 24 mm, Depth: 1 mm, V-2
Order No.	0297700000
Type	AD 3 SAK6N
GTIN (EAN)	4008190086787
Qty.	50 pc(s).

AD 3 SAK6N

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	1 mm	Depth (inches)	0.039 inch
Height	25 mm	Height (inches)	0.984 inch
Width	24 mm	Width (inches)	0.945 inch
Net weight	0.76 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Material data

Material	PVC	Colour	yellow
UL 94 flammability rating	V-2		

System specifications

Version	End and intermediate plate
---------	----------------------------

Additional technical data

Installation advice	Direct mounting	Snap-on	No
---------------------	-----------------	---------	----

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92
ECLASS 13.0	27-25-03-90	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format