

KISC M3X15/6 SAK2.5 CU5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Depending on the terminal block or also accessories, we offer different types of screws as additional items or also spare parts.

General ordering data

Version	SAK Series, Mounting screw, Steel
Order No.	0377200000
Type	KISC M3X15/6 SAK2.5 CU5
GTIN (EAN)	4008190006389
Qty.	100 pc(s).

KISC M3X15/6 SAK2.5 CU5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	17 mm	Depth (inches)	0.669 inch
Height	4.8 mm	Height (inches)	0.189 inch
Width	4.8 mm	Width (inches)	0.189 inch
Net weight	1 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Material data

Material	Steel	Surface finish	Miscellaneous
Colour	grey		

System specifications

Version	for busbars
---------	-------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Dimensions

Metric size of the thread, external	3 mm
-------------------------------------	------

General

Installation advice	Direct mounting	Surface finish	Miscellaneous
---------------------	-----------------	----------------	---------------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92
ECLASS 13.0	27-25-03-90	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%