

PAC-UNIV-D37M-F-10M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

Version	Pre-assembled cable, PAC, Cable LiYCY, 12.2 ± 1 mm
Order No.	1350440100
Type	PAC-UNIV-D37M-F-10M
GTIN (EAN)	4032248391806
Qty.	1 pc(s).

PAC-UNIV-D37M-F-10M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 2,525 g

Temperatures

Storage temperature -10...60 °C Operating temperature -10...50 °C

General Data

Cable	Cable LiYCY	Cable length	10 m
Connector PLC side	H0.25/10 (FERRULES 0.25mm ²)	Interface connector	SUB-D MALE 37P
Material	PVC	Number of poles, min.	37-pole
Outer diameter	12.2 ± 1 mm	Suitable for	Analogue signals
Wire cross-section	0.25 mm ²		

Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 Vdc ≤ 25 Vac	Resistance	≤ 80 mΩ/m
Total current, max.	3 A		

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20
ECLASS 13.0	27-24-22-20	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	4bbf2c0d-0764-4fc8-bb24-9351c28c190d

Approvals

ROHS Conform

Downloads

User Documentation	Colours chart
Catalogues	Catalogues in PDF-format