

IE-FM5Z2LO0010MST0ST0-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE cables, FO

General ordering data

Version	Patch cable, ST IP 20, ST IP 20, 50 µm, LSZH, 10 m
Order No.	1433990100
Type	IE-FM5Z2LO0010MST0ST0-X
GTIN (EAN)	4050118242775
Qty.	1 pc(s).

IE-FM5Z2LO0010MST0ST0-X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	10 m	Length (inches)	393.701 inch
Net weight	152 g		

Temperatures

Operating temperature	-20 °C...70 °C
-----------------------	----------------

Cable specific standards

Specification for checking the symmetrical communication cabling	IEC 61935-3	Specification for twisted-pair device connection cables	IEC 61156-6, DIN EN 50288-4-2
--	-------------	---	-------------------------------

General standards

Connector standard	IEC 60874-10
--------------------	--------------

Standards

Connector standard	IEC 60874-10
--------------------	--------------

Fibre-optic

Attenuation	≤2.5 dB/km at 850 nm, ≤0.7 dB/km at 1300 nm	Bandwidth	≥ 500 MHz*km at 850 nm, ≥ 500 MHz*km at 1300 nm
Fibre type	GOF, Multimode, OM2		

Cable structure

Cable layout	ZIPCORD	Core diameter	50 µm
Material sheath	LSZH	Primary coating	245 µm
Sheath diameter	2.8 * 5.7 mm	Sheathing colour	orange
Standard designations	I-V(ZN)H		

Mechanical and material properties of cable

Halogen	No	Min. bending radius, once only	28 mm
Min. bending radius, repetitive	56 mm		

Plug

Plug left	ST, IP20, male contact, straight, plug, Plastic, unshielded	Plug right	ST, IP20, male contact, straight, plug, Plastic, unshielded
-----------	---	------------	---

Plug, left

Plug left	ST, IP20, male contact, straight, plug, Plastic, unshielded
-----------	---

Plug, right

Plug right	ST, IP20, male contact, straight, plug, Plastic, unshielded
------------	---

Creation date July 13, 2025 10:27:05 AM CEST

Catalogue status 04.07.2025 / We reserve the right to make technical changes.

IE-FM5Z2LO0010MST0ST0-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03
ECLASS 13.0	27-06-10-03	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-FM5Z2LO0010MST0ST0-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing



IE-FM5Z2LO0010MST0ST0-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****V0 material**

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	VT SF 5/21 MC NE WS V0	Version
Order No.	1689470001	SlimFix, Conductor and cable markers, 4.8 - 7.4 mm, 21 x 7.4 mm,
GTIN (EAN)	4008190872571	white
Qty.	160 pc(s).	
Type	VT SF 6/21 MC NE WS V0	Version
Order No.	1730560001	SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm,
GTIN (EAN)	4008190954611	white
Qty.	160 pc(s).	