

KLBUE 10-20 SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The shield clamping saddles for direct mounting can be easily and conveniently attached directly to the mounting plate. The products differ in the range of the cable diameter and the thread for fastening the shield clamping saddles.

General ordering data

Version	Clamping yoke, Clamping yoke
Order No.	1791240000
Type	KLBUE 10-20 SC
GTIN (EAN)	4032248222193
Qty.	100 pc(s).

KLBUE 10-20 SC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.575 inch
Height	26 mm	Height (inches)	1.024 inch
Width	23.6 mm	Width (inches)	0.929 inch
Mounting dimension - width	22.1 mm	Net weight	29.216 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Material data

Colour	silver	UL 94 flammability rating	None
--------	--------	---------------------------	------

System specifications

Version	For a shield connection	End cover plate required	No
Rail	Mounting plate		

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of mounting	Screw		

Conductors for clamping (rated connection)

Cable diameter, max.	20 mm	Cable diameter, min.	10 mm
Connection cross-section, stranded, max.	20 mm ²	Connection cross-section, stranded, min.	10 mm ²
Stripping length	26 mm	Type of connection	Spring connection

General

Installation advice	Direct mounting	Rail	Mounting plate
---------------------	-----------------	------	----------------

Rating data

Rated cross-section	20 mm ²
---------------------	--------------------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50
ECLASS 13.0	27-25-01-20	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		

Approvals

ROHS	Conform
------	---------

Cradle to gate

0.099 kg CO₂ eq.

KLBUE 10-20 SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	de.myview.objectmodel.impl.BlockImpl@f1a33ea

Downloads

Engineering Data	CAD data – STEP CAD data – DWG CAD data – DXF
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format