

CBFP 43.5/10 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Fastening of cables or bundles with ties into electrical switchgears and cabinets.

General ordering data

Version	Cable ties, 10 x 10 mm, Plastic, 80 N
Order No.	1859410000
Type	CBFP 43.5/10 BK
GTIN (EAN)	4032248412297
Qty.	100 pc(s).

CBFP 43.5/10 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	2 mm	Depth (inches)	0.079 inch
Height	10 mm	Height (inches)	0.394 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	1.91 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Installation materials

Diameter of fastening hole	8 mm	For re-opening	No
Halogen	No	Material	Plastic
Max. cable tie width	9 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Tensile strength	80 N
Tensile strength (Pound-force)	18 lbf	UL 94 flammability rating	V-2
UV-resistant	No	Version	for wall mounting

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02
ECLASS 13.0	27-14-07-02	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CBFP 43.5/10 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Dimensional drawing

