

SCREWTY M12 KO O. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The Screwty® attachment is suitable for M12 round plug-in connectors, with an outside dimension of the knurled nut of 14.5 ± 0.3 mm. The tightening torque is 0.8-1.2 Nm.

General ordering data

Version	Cable gland tool adapter for moulded M12 lines
Order No.	1900100000
Type	SCREWTY M12 KO O. SD
GTIN (EAN)	4032248409952
Qty.	1 pc(s).
Packaging	Plastic bag

SCREWTY M12 KO O. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	16 g
------------	------

Screwing tools

Connection thread	M12	Size	14.5 mm
-------------------	-----	------	---------

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-01-90-90	ECLASS 12.0	21-01-90-90
ECLASS 13.0	21-01-90-90	ECLASS 14.0	21-01-90-90
ECLASS 15.0	21-01-90-90		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN