

DGSB IP30 D0 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Intelligent cabling solutions can save you valuable time and money.**

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread
Integration of operating and signalling devices into the seal possible

General ordering data

Version	Field Power® sealing insert, Blank seal, IP30, with corresponding enclosure, TPE-U
Order No.	1967600000
Type	DGSB IP30 D0 PT6
GTIN (EAN)	4032248688746
Qty.	10 pc(s).

DGSB IP30 D0 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	3.15 mm	Depth (inches)	0.124 inch
Height	23.51 mm	Height (inches)	0.926 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	1.6 g		

Temperatures

Storage temperature	-40 °C...55 °C	Operating temperature	-40 °C...55 °C
---------------------	----------------	-----------------------	----------------

General data

Material	TPE-U	Silicone	No
Colour	grey	Design	Blank seal
Protection degree	IP30, with corresponding enclosure	Mounting position, installation notice	in FieldPower® IP30 sealing slot

Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 9.1	27-18-27-90
ECLASS 10.0	27-18-28-15	ECLASS 11.0	27-18-28-15
ECLASS 12.0	27-18-28-15	ECLASS 13.0	27-18-28-15
ECLASS 14.0	27-18-28-15	ECLASS 15.0	27-18-28-15

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration FieldPower® BOX, BOX FUSE and Terminal variants
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format