

ES EPG 45 WM 150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	150mm ² , WM crimp
Order No.	1994550000
Type	ES EPG 45 WM 150
GTIN (EAN)	4050118379785
Qty.	1 pc(s).

ES EPG 45 WM 150

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	12 mm	Depth (inches)	0.472 inch
Height	60 mm	Height (inches)	2.362 inch
Width	30 mm	Width (inches)	1.181 inch
Net weight	2.75 g		

Crimp inserts

Crimp cross-section copper	150	Crimping width	5 mm
Crimping width in mm	5		

Description of contact

Conductor cross-section, max. AWG	5/0	Conductor cross-section, min. AWG	5/0
Crimping range, max.	150 mm ²		

tool data crimping

Cable lug cross section	nominal	150 mm ²
Crimping type/profile	WM crimp	

Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90
ECLASS 13.0	21-04-90-90	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
------------	--

ES EPG 45 WM 150

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

10 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KP-M10/-150	Version
Order No.	1498310000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307801	
Qty.	25 pc(s).	

150 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KWPN-M20/150 90	Version
Order No.	1496680000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118306088	
Qty.	25 pc(s).	
Type	KWPN-M12/-150 90	Version
Order No.	1497820000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307306	
Qty.	25 pc(s).	
Type	KWPN-M10/-150 90	Version
Order No.	1497810000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307221	
Qty.	25 pc(s).	
Type	KWPN-M8/-150 90	Version
Order No.	1497790000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307085	
Qty.	25 pc(s).	

ES EPG 45 WM 150

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	KWPN-M16/-150 90	Version
Order No.	1497830000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307160	
Qty.	25 pc(s).	

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	EPG 45	Version
Order No.	1500830000	Pressing tool, 6mm ² , 150mm ² , Hexagonal crimp, WM crimp, Indent
GTIN (EAN)	4050118309317	crimp, Trapezoidal crimp, Oval crimping
Qty.	1 pc(s).	

150 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KP-M8/-150	Version
Order No.	1498290000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307399	
Qty.	25 pc(s).	

Type	KP-M20/-150	Version
Order No.	1498340000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307740	
Qty.	25 pc(s).	

ES EPG 45 WM 150

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Type	KP-M12/-150	Version
Order No.	1498320000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307658	
Qty.	25 pc(s).	
Type	KP-M14/-150	Version
Order No.	1498580000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118308112	
Qty.	25 pc(s).	
Type	KP-M16/-150	Version
Order No.	1498330000	cable lug, terminal end, 150 mm ²
GTIN (EAN)	4050118307641	
Qty.	25 pc(s).	

150 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M8/-150	Version
Order No.	1495700000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305333	
Qty.	25 pc(s).	
Type	KRN-M14/-150	Version
Order No.	1495810000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305500	
Qty.	25 pc(s).	
Type	KRN-M20/-150	Version
Order No.	1495740000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305357	
Qty.	25 pc(s).	
Type	KRN-M12/-150	Version
Order No.	1495720000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305296	
Qty.	25 pc(s).	
Type	KRN-M10/-150	Version
Order No.	1495710000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305159	
Qty.	25 pc(s).	
Type	KRN-M16/-150	Version
Order No.	1495730000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305395	
Qty.	25 pc(s).	

ES EPG 45 WM 150

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

150 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KWN-M10/-150 90	Version
Order No.	1494500000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118303896	
Qty.	25 pc(s).	
Type	KWN-M20/-150 90	Version
Order No.	1494530000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304206	
Qty.	25 pc(s).	
Type	KWN-M16/-150 90	Version
Order No.	1494520000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118303995	
Qty.	25 pc(s).	
Type	KWN-M12/-150 90	Version
Order No.	1494510000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304305	
Qty.	25 pc(s).	
Type	KWN-M8/-150 90	Version
Order No.	1494490000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304107	
Qty.	25 pc(s).	

ES EPG 45 WM 150

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

150 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KWN-M8/-150 45	Version
Order No.	1496430000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118306071	
Qty.	25 pc(s).	
Type	KWN-M16/-150 45	Version
Order No.	1496470000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118306132	
Qty.	25 pc(s).	
Type	KWN-M10/-150 45	Version
Order No.	1496440000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305777	
Qty.	25 pc(s).	
Type	KWN-M20/-150 45	Version
Order No.	1496480000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305739	
Qty.	25 pc(s).	
Type	KWN-M12/-150 45	Version
Order No.	1496450000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118305906	
Qty.	25 pc(s).	

ES EPG 45 WM 150

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

150 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M10/-150 S	Version
Order No.	1494950000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304473	
Qty.	10 pc(s).	
Type	KRN-M8/-150 S	Version
Order No.	1494940000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304701	
Qty.	10 pc(s).	
Type	KRN-M6/-150 S	Version
Order No.	1494440000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118303964	
Qty.	10 pc(s).	
Type	KRN-M12/-150 S	Version
Order No.	1494970000	cable lug, terminal end, 150 mm ² , 150 mm ² - 150 mm ²
GTIN (EAN)	4050118304459	
Qty.	10 pc(s).	

150 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	VPN/-150	Version
Order No.	1498710000	cable lug, terminal end, 150 mm ² , 150 mm ² , None
GTIN (EAN)	4050118308129	
Qty.	25 pc(s).	

ES EPG 45 WM 150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****150 mm²**

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	VPLN/-150	Version
Order No.	1492970000	cable lug, terminal end, 150 mm ² , 150 mm ² , None
GTIN (EAN)	4050118302912	
Qty.	50 pc(s).	