

WCU 501 RS232 CABLE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

With the fully encapsulated WCU 501 and WCU 650 logic modules, you monitor, control and regulate your processes - even under extreme environmental conditions. In this regard, the WCU series offers optimum dimensions, performance, robustness and user-friendliness. The graphic and intuitive Micon-L programming environment enables flexible switching of the analogue and digital inputs, plus the digital outputs too. The scope of both the software and the hardware can be expanded to suit customer requirements upon request. .

General ordering data

Version	universal, USB 2.0
Order No.	2515030000
Type	WCU 501 RS232 CABLE
GTIN (EAN)	4050118528756
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2024-06-30

WCU 501 RS232 CABLE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	200 mm	Length (inches)	7.874 inch
Net weight	43 g		

Temperatures

Storage temperature	-30 °C...60 °C	Operating temperature	-20 °C...60 °C
---------------------	----------------	-----------------------	----------------

Connection data

Type of connection	9-pole SUB-D socket (female)
--------------------	------------------------------

General data

Vibration resistance	min. 50 m/s ² (5 g) @ 10...150 Hz
----------------------	--

System data

Interface	Seriell RS232
-----------	---------------

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20
ECLASS 13.0	27-24-22-20	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--