

SCREWTY M12 K+L 2.5 O.SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

General ordering data

Version	Cable gland tool adapter for moulded M12 lines, K- and L-coded
Order No.	2522710000
Type	SCREWTY M12 K+L 2.5 O.SD
GTIN (EAN)	4050118534566
Qty.	1 pc(s).
Packaging	Plastic bag

SCREWTY M12 K+L 2.5 O.SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	18.8 g
------------	--------

Screwing tools

Connection thread	M12	Size	17.5 mm
-------------------	-----	------	---------

Classifications

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 9.0	21-04-50-03
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-50-03
ECLASS 11.0	21-01-90-90	ECLASS 12.0	21-01-90-90
ECLASS 13.0	21-01-90-90	ECLASS 14.0	21-01-90-90
ECLASS 15.0	21-01-90-90		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
------------	--