

WIL-BM-SK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Motion detector for the WIL-LED luminaire with screw connection. Switching time adjustable.

General ordering data

Order No.	2537720000
Type	WIL-BM-SK
GTIN (EAN)	4050118549157
Qty.	1 pc(s).

WIL-BM-SK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	44 mm	Depth (inches)	1.732 inch
Height	33 mm	Height (inches)	1.299 inch
Width	76 mm	Width (inches)	2.992 inch
Net weight	33 g		

Temperatures

Operating temperature	-20 - 60°C
-----------------------	------------

Connection data

Connection thread	Terminal	Wiring	PIN 4: + (black), PIN 3: - (blue)
-------------------	----------	--------	-----------------------------------

Electric data

Rated voltage	24 V DC	Rated current	< 6.0 A
---------------	---------	---------------	---------

General technical data

Protection degree	IP20
Dwell time, min.	1 min
Dwell time, max.	10 min
Detection range	min. 0 m
	max. 8 m
	Configurable No
Detection area (angle)	120 °

Classifications

ETIM 6.0	EC000133	ETIM 7.0	EC000133
ETIM 8.0	EC000133	ETIM 9.0	EC000133
ETIM 10.0	EC000133	ECLASS 9.1	27-14-40-07
ECLASS 10.0	27-14-40-07	ECLASS 11.0	27-14-40-07
ECLASS 12.0	27-14-40-07	ECLASS 13.0	27-14-40-07
ECLASS 14.0	27-14-40-07	ECLASS 15.0	27-14-40-07

Approvals

Approvals

Approvals MAMID https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/

ROHS Conform

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	82a8bf14-9104-4ca4-ab0c-226d976fdcac

WIL-BM-SK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)