

CD-SE 40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Version	Cable duct separator, 40 mm x
Order No.	2553970000
Type	CD-SE 40
GTIN (EAN)	4050118564105
Qty.	60 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31

CD-SE 40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	40 mm	Height (inches)	1.575 inch
Length	1,000 mm	Length (inches)	39.37 inch
Net weight	7.167 g		

Temperatures

Operating temperature range	-5...60 °C
-----------------------------	------------

General information

Colour	grey	Material	PVC
Non-tracking	Yes	Operating temperature range	-5...60 °C
UL 94 flammability rating	V-0	Version	1-wall

Classifications

ETIM 6.0	EC001015	ETIM 7.0	EC001015
ETIM 8.0	EC001015	ETIM 9.0	EC001015
ETIM 10.0	EC001015	ECLASS 9.1	27-40-07-52
ECLASS 10.0	27-40-07-52	ECLASS 11.0	27-40-07-52
ECLASS 12.0	27-40-07-52	ECLASS 13.0	27-40-07-52
ECLASS 14.0	27-40-07-52	ECLASS 15.0	27-40-07-52

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
------------	--