

CD-RETA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Version	Cable duct binder arm, 8 mm x 115.3 mm
Order No.	2554080000
Type	CD-RETA
GTIN (EAN)	4050118564204
Qty.	100 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31

CD-RETA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	20 mm	Depth (inches)	0.787 inch
Height	8 mm	Height (inches)	0.315 inch
Width	115.3 mm	Width (inches)	4.539 inch
Net weight	3 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General information

Channel width	40-120	Colour	yellow
Material	Polyamide 6 (PA 6)	Non-tracking	Yes
Operating temperature range	-40...100 °C	UL 94 flammability rating	HB
Usage	For all wiring ducts (up to max. 105 mm wide)		

Classifications

ETIM 6.0	EC001018	ETIM 7.0	EC001018
ETIM 8.0	EC001018	ETIM 9.0	EC001018
ETIM 10.0	EC001018	ECLASS 9.0	27-40-07-65
ECLASS 9.1	27-40-07-65	ECLASS 10.0	27-40-07-65
ECLASS 11.0	27-40-07-65	ECLASS 12.0	27-40-07-65
ECLASS 13.0	27-40-07-65	ECLASS 14.0	27-40-07-65
ECLASS 15.0	27-40-07-65		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
------------	--