

RFF-FIMT 605X 54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

General ordering data

Version	Filter mat, IP54, white
Order No.	2557750000
Type	RFF-FIMT 605X 54
GTIN (EAN)	4050118568394
Qty.	20 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31

RFF-FIMT 605X 54**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	70 mm	Height (inches)	2.756 inch
Width	290 mm	Width (inches)	11.417 inch
Net weight	17.35 g		

Temperatures

Operating temperature range	-15...55 °C
-----------------------------	-------------

General data

Colour	white	Filter class	G 4
Operating temperature range	-15...55 °C	Protection class (UL)	Type 12
Type of mounting	when screwed in		

Classifications

ETIM 6.0	EC000320	ETIM 7.0	EC000320
ETIM 8.0	EC000320	ETIM 9.0	EC000320
ETIM 10.0	EC000320	ECLASS 9.1	27-18-07-16
ECLASS 10.0	27-18-07-16	ECLASS 11.0	27-18-07-16
ECLASS 12.0	27-18-07-16	ECLASS 13.0	27-18-07-16
ECLASS 14.0	27-18-07-16	ECLASS 15.0	27-18-07-16

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	Operating instructions
Catalogues	Catalogues in PDF-format