

**CD-LID 75 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

|                 |                                                                |
|-----------------|----------------------------------------------------------------|
| Version         | Cable duct cover, 75 mm                                        |
| Order No.       | <a href="#">2590030000</a>                                     |
| Type            | CD-LID 75 GY                                                   |
| GTIN (EAN)      | 4050118600735                                                  |
| Qty.            | 2 m                                                            |
| Delivery status | <b>This article will no longer be available in the future.</b> |
| Available until | 2025-12-31                                                     |

**CD-LID 75 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Width      | 75 mm    | Width (inches)  | 2.953 inch |
| Length     | 2,000 mm | Length (inches) | 78.74 inch |
| Net weight | 133.34 g |                 |            |

**Temperatures**

|                             |            |
|-----------------------------|------------|
| Operating temperature range | -5...60 °C |
|-----------------------------|------------|

**General information**

|                             |                 |                      |         |
|-----------------------------|-----------------|----------------------|---------|
| Colour                      | grey            | Flexible wiring duct | No      |
| Halogen                     | Yes             | Lid                  | Yes     |
| Material                    | PVC / lead-free | Non-tracking         | Yes     |
| Operating temperature range | -5...60 °C      | Type of mounting     | Snap-on |
| UL 94 flammability rating   | V-0             |                      |         |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000727    | ETIM 7.0    | EC000727    |
| ETIM 8.0    | EC000727    | ETIM 9.0    | EC000727    |
| ETIM 10.0   | EC000727    | ECLASS 9.1  | 27-40-07-76 |
| ECLASS 10.0 | 27-40-07-76 | ECLASS 11.0 | 27-40-07-76 |
| ECLASS 12.0 | 27-40-07-76 | ECLASS 13.0 | 27-40-07-76 |
| ECLASS 14.0 | 27-40-07-76 | ECLASS 15.0 | 27-40-07-76 |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|