


CB-UVR 365/7,5 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

UV-resistant polyamide 6.6 ensures long durability of our special cable ties even with strong UV radiation. Ideal for continuous outdoor use.

General ordering data

Version	Cable ties, 7.5 x 365 mm, Polyamide 66, 540 N
Order No.	2659360000
Type	CB-UVR 365/7,5 BK
GTIN (EAN)	4050118682823
Qty.	100 pc(s).

CB-UVR 365/7,5 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	1 mm	Depth (inches)	0.039 inch
Height	365 mm	Height (inches)	14.37 inch
Width	7.5 mm	Width (inches)	0.295 inch
Net weight	4.21 g		

Temperatures

Operating temperature range	-40...85 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	105 °C		

Installation materials

Bundle diameter, max.	100 mm	Bundle diameter, min.	8 mm
Cable diameter, max.	100 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	540 N	Tensile strength (Pound-force)	121 lbf
UL 94 flammability rating	V-2	UV-resistant	Yes

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ETIM 10.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02
ECLASS 13.0	27-14-07-02	ECLASS 14.0	27-14-07-02
ECLASS 15.0	27-14-07-02		

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Catalogues	Catalogues in PDF-format

CB-UVR 365/7,5 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

