

BIT E6,3 PH2X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Crosshead bits are Phillips-Recessed type PH/DIN 5260.

1/4" drive, E6.3 DIN 3126

General ordering data

Version	Screwdriver insert, Blade width (B): 2 mm, Blade length: 70 mm, Blade thickness (A): 2 mm, Blade size, crosshead: 2
Order No.	2748990000
Type	BIT E6,3 PH2X70
GTIN (EAN)	4050118895186
Qty.	5 pc(s).

BIT E6,3 PH2X70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Width	70 mm	Width (inches)	2.756 inch
Net weight	15.2 g		

Technical data

Description of article	Bit with crosshead, Phillips size 2
------------------------	-------------------------------------

Screwing tools

Blade length	70 mm	Blade size, crosshead	2
Blade thickness (A)	2 mm	Blade width (B)	2 mm
Form	E 6.3 DIN 3126, Crosshead	Size	2

Classifications

ETIM 6.0	EC002115	ETIM 7.0	EC002115
ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 9.1	21-04-04-90
ECLASS 10.0	21-04-04-90	ECLASS 11.0	21-04-42-03
ECLASS 12.0	21-04-42-03	ECLASS 13.0	21-04-42-03
ECLASS 14.0	21-04-42-03	ECLASS 15.0	21-04-42-03

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--