

US67-PLATE64-STD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller offers high-quality cables, plugs, mounting adapters and magnets for the professional and industrial installation of vibration monitors.

General ordering data

Version	Adapter plate
Order No.	2811910000
Type	US67-PLATE64-STD
GTIN (EAN)	4064675292975
Qty.	1 pc(s).

US67-PLATE64-STD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	64 mm	Depth (inches)	2.52 inch
Height	11.5 mm	Height (inches)	0.453 inch
Width	64 mm	Width (inches)	2.52 inch
Diameter	64 mm	Net weight	132 g

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...85 °C
Humidity at operating temperature	5...95 % rel. humidity, no condensation		

General data

Is an accessory	Yes	Type of accessory	Mounting accessories
-----------------	-----	-------------------	----------------------

Installation

Type of thread	metric
----------------	--------

Classifications

ETIM 7.0	EC003015	ETIM 8.0	EC003015
ETIM 9.0	EC003015	ETIM 10.0	EC003015
ECLASS 9.1	27-20-14-92	ECLASS 10.0	27-20-14-92
ECLASS 11.0	27-20-14-92	ECLASS 12.0	27-20-14-92
ECLASS 13.0	27-20-14-92	ECLASS 14.0	27-20-14-92
ECLASS 15.0	27-20-14-92		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Quick start guide – IS US67-PLATE64-STD
Catalogues	Catalogues in PDF-format

US67-PLATE64-STD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

