

US67-USB-STICK-BLE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller offers high-quality cables, plugs, mounting adapters and magnets for the professional and industrial installation of vibration monitors.

General ordering data

Version	Communication module
Order No.	2874720000
Type	US67-USB-STICK-BLE
GTIN (EAN)	4064675649526
Qty.	1 pc(s).

US67-USB-STICK-BLE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	43 mm	Depth (inches)	1.693 inch
Height	16 mm	Height (inches)	0.63 inch
Width	11 mm	Width (inches)	0.433 inch
Net weight	7 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-30 °C...85 °C
Humidity at operating temperature	5...95 % rel. humidity, no condensation		

General data

Is a replacement part	Yes
-----------------------	-----

Communication

Antenna characteristics	integrated	Communication range, max., line-of sight	90 m
Communication range, max., in shop floor	30 m	Bluetooth module	Bluetooth Low Energy

Classifications

ETIM 7.0	EC000310	ETIM 8.0	EC000310
ETIM 9.0	EC000310	ETIM 10.0	EC000310
ECLASS 9.1	19-05-01-10	ECLASS 10.0	19-05-01-10
ECLASS 11.0	19-05-01-10	ECLASS 12.0	19-05-01-10
ECLASS 13.0	19-05-01-10	ECLASS 14.0	19-05-01-10
ECLASS 15.0	19-05-01-10		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Downloads

User Documentation	Quick start guide – IS US67-USB-STICK-BLE
Catalogues	Catalogues in PDF-format