

KT MINI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Version	Cutting tools
Order No.	2876460000
Type	KT MINI
GTIN (EAN)	4064675664024
Qty.	1 pc(s).

KT MINI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	9.5 mm	Depth (inches)	0.374 inch
Height	120 mm	Height (inches)	4.724 inch
Width	42 mm	Width (inches)	1.654 inch
Length	120 mm	Length (inches)	4.724 inch
Net weight	91 g		

Technical data

Description of article	Cutting tool for up to 12 mm outer diameter	Operating voltage	1,000 V
Version	One-hand mechanical		

Cutting tools

Copper cable - flexible, max.	16 mm ²	Copper cable - flexible, max. (AWG)	6 AWG
Copper cable - solid, max.	35 mm ²	Copper cable - solid, max. (AWG)	2 AWG
Copper cable - stranded, max.	25 mm ²	Copper cable - stranded, max. (AWG)	4 AWG
Copper cable, max. diameter	7 mm	Operating voltage	1,000 V
Single-core aluminium cable, max.(mm ²)	35 mm ²	Stranded aluminium cable, max (mm ²)	25 mm ²
Stranded aluminium cable, max. (AWG)	4 AWG	Stranded aluminium cable, max. diameter	7 mm

Classifications

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 9.0	21-04-47-01
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-47-01
ECLASS 11.0	21-04-47-01	ECLASS 12.0	21-04-47-01
ECLASS 13.0	21-04-47-01	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

Catalogues	Catalogues in PDF-format
------------	--