

ZQV 6SL/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles: 3, Pitch in mm (P): 8.20, Insulated: Yes, Width: 22.9 mm
Order No.	3077590000
Type	ZQV 6SL/3
GTIN (EAN)	4099987081795
Qty.	25 pc(s).

ZQV 6SL/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	29.6 mm	Depth (inches)	1.165 inch
Height	29.6 mm	Height (inches)	1.165 inch
Width	22.9 mm	Width (inches)	0.902 inch
Net weight	2.818 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Material data

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

Additional technical data

Explosion-tested version	Yes	Type of fixing	Plugged
Type of mounting	Direct mounting		

Dimensions

Pitch in mm (P)	8.2 mm
-----------------	--------

General

Number of poles	3
-----------------	---

Rating data

Rated voltage	400 V	Rated current	41 A
---------------	-------	---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40
ECLASS 13.0	27-25-03-03	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Engineering Data	CAD data – STEP
------------------	---------------------------------

Creation date June 25, 2025 11:02:12 AM CEST