

FPL 7G2.5C/Q8MW/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

General ordering data

Version	FieldPower®, Cable, Metal housing, Number of wires: 7, Ölflex Classic 110 CY 7G2.5 or similar, Cross-section: 2.5 mm ² , 3 m
Order No.	8000011751
Type	FPL 7G2.5C/Q8MW/3
GTIN (EAN)	4050118190434
Qty.	1 pc(s).

FPL 7G2.5C/Q8MW/3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	1,349 g
------------	---------

Classifications

ETIM 6.0	EC001578	ETIM 7.0	EC003250
ETIM 8.0	EC003250	ETIM 9.0	EC003250
ETIM 10.0	EC003250	ECLASS 9.0	27-06-20-11
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-01-06
ECLASS 11.0	27-06-01-06	ECLASS 12.0	27-06-01-06
ECLASS 13.0	27-06-01-06	ECLASS 14.0	27-06-01-06
ECLASS 15.0	27-06-01-06		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	edb4769d-47d5-4f66-921a-c1f4685d793c

Downloads

Catalogues	Catalogues in PDF-format
------------	--

FPL 7G2.5C/Q8MW/3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Pin assignments

	Pin	Conductor	Assignment
8 = NC	1	1	U
	2	-	-
5 = NC	3	3	W
	4	4	Brake
⊕ = PE	5	-	-
	6	5	Brake
3 = W	7	2	V
2 = NC	8	-	-
	PE	gr./yell.	PE