

SSR 24V ACDC/24 VDC 5A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**General ordering data**

Version	Solid-state relay, Rated control voltage: 15 V UC...30 V UC , Rated switching voltage: 0...30 V DC, Continuous current: 5 A, Plug-in connection
Order No.	8576350000
Type	SSR 24V ACDC/24 VDC 5A
GTIN (EAN)	4032248230525
Qty.	15 pc(s).
Available until	2016-12-31
Alternative product	1421450000

Creation date July 9, 2025 9:29:46 AM CEST

Catalogue status 04.07.2025 / We reserve the right to make technical changes.

SSR 24V ACDC/24 VDC 5A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	25 mm	Depth (inches)	0.984 inch
Height	29.2 mm	Height (inches)	1.15 inch
Width	13 mm	Width (inches)	0.512 inch
Net weight	16.87 g		

Temperatures

Storage temperature	-40 °C...50 °C	Operating temperature	-40 °C...50 °C
---------------------	----------------	-----------------------	----------------

Control side

Rated control voltage	15 V UC...30 V UC	Nominal control current	9 mA DC (±10%)
Power rating	220 mW	Status indicator	No
Input frequency	10 Hz		

Load side

Rated switching voltage	0...30 V DC	Continuous current	5 A
Rated switching current	5 A	Switch-on delay	< 2 ms
Switch-off delay	< 20 ms	Voltage drop at max. load	≤ 0.5 V
Leakage current	< 1 mA	Short-circuit-proof	No
Contact type	1 NO contact (Bipolar transistor)	max. switching frequency (DC control voltage)	10 Hz

General data

Colour	Light Blue
--------	------------

Insulation coordination

Rated voltage	300 V	Surge voltage category	III
Clearance and creepage distances for control side - load side	> 8 mm	Impulse withstand voltage	2.5 kV (1.2/50 µs)

Connection data

Wire connection method	Plug-in connection
------------------------	--------------------

Classifications

ETIM 6.0	EC001504	ETIM 7.0	EC001504
ETIM 8.0	EC001504	ETIM 9.0	EC001504
ETIM 10.0	EC001504	ECLASS 9.0	27-37-16-04
ECLASS 9.1	27-37-16-04	ECLASS 10.0	27-37-16-04
ECLASS 11.0	27-37-16-04	ECLASS 12.0	27-37-16-04
ECLASS 13.0	27-37-16-04	ECLASS 14.0	27-37-16-04
ECLASS 15.0	27-37-16-04		

Data sheet**SSR 24V ACDC/24 VDC 5A****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Technical data****Approvals**

Approvals



Approvals MAMID

https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/

ROHS

Conform

Environmental Product Compliance

RoHS Compliance Status

Compliant

REACH SVHC

No SVHC above 0.1 wt%

Downloads

Catalogues

[Catalogues in PDF-format](#)