

IE-FM6D2UE0005MST0ST0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE cables, FO breakout cable, multimode, SC duplex - SC duplex, black, Core diameter 62.5 µm

General ordering data

Version	Dragline cable, ST, ST IP 20, 62.5 µm, PUR, 5 m
Order No.	8876460050
Type	IE-FM6D2UE0005MST0ST0X
GTIN (EAN)	4032248610051
Qty.	1 pc(s).

IE-FM6D2UE0005MST0ST0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	5 m	Length (inches)	196.85 inch
Net weight	100 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-20 °C...60 °C		

General standards

Connector standard	IEC 61754-2
--------------------	-------------

Standards

Connector standard	IEC 61754-2
--------------------	-------------

Fibre-optic

Attenuation	2.7 dB/km at 850 nm, ≤ 0.5 dB/km at 1300 nm	Bandwidth	200 MHz*km at 850 nm, 500 MHz*km at 1300 nm
Fibre type	GOF, Multimode, OM1	Insertion loss	≤ 0.4 dB
Return loss (attenuation)	≥ 30 dB		

Cable structure

Cable layout	Break-out dragline	Core diameter	62.5 µm
Material sheath	PUR	Primary coating	245 µm
Sheath diameter	6 mm	Sheathing colour	black

Mechanical and material properties of cable

Bending cycles	100,000	Min. bending radius, once only	25 mm
Min. bending radius, repetitive	77 mm		

Plug

Plug left	ST, IP20, male contact, straight, plug, Plastic, un- shielded	Plug right	ST, IP20, male contact, straight, plug, Plastic, un- shielded
-----------	---	------------	---

Plug, left

Plug left	ST, IP20, male contact, straight, plug, Plastic, un- shielded
-----------	---

Plug, right

Plug right	ST, IP20, male contact, straight, plug, Plastic, un- shielded
------------	---

IE-FM6D2UE0005MST0ST0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03
ECLASS 13.0	27-06-10-03	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-FM6D2UE0005MST0ST0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Detailed drawing

