

LG DMS PRO/ DMS 3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

General ordering data

Version	DMS 3, 90 % bei 3x 500 V AC / > 91 % bei 3 x 400 V AC
Order No.	9007460000
Type	LG DMS PRO/ DMS 3
GTIN (EAN)	4008190404970
Qty.	1 pc(s).

LG DMS PRO/ DMS 3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	178 mm	Depth (inches)	7.008 inch
Height	78 mm	Height (inches)	3.071 inch
Width	150 mm	Width (inches)	5.905 inch
Length	178 mm	Length (inches)	7.008 inch
Net weight	604.79 g		

Technical data

Description of article	Mains-operated torque screwdriver with 1/4" drive	Electrical connection	220 - 240 V / 50 - 60 Hz
Voltage range	12 / 14.4 / 18 V		

Electric screwdriver

Battery voltage	3.6 V	Bit holder	1/4" DIN 3126 Form E6.3
Charger input	AC 220-240V~50-60Hz 30W	Charger output	DC 2.8...6V; 4.8A / 30W max.
Idling speed	200 u. 600 min ⁻¹	Max. coupling torque	3 Nm
Rated voltage	3.6 V	Weight	600 g
Weight of charger	600 g		

Classifications

ETIM 6.0	EC000359	ETIM 7.0	EC000359
ETIM 8.0	EC000359	ETIM 9.0	EC000359
ETIM 10.0	EC000359	ECLASS 9.1	21-05-92-01
ECLASS 10.0	21-05-92-01	ECLASS 11.0	21-05-29-01
ECLASS 12.0	21-05-29-01	ECLASS 13.0	21-05-29-01
ECLASS 14.0	21-05-29-01	ECLASS 15.0	21-05-29-01

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/
ROHS	Conform

Downloads

Catalogues	Catalogues in PDF-format
Brochures	