

EINSATZPAAR PZ 16E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Version	16mm ² , Indent crimp
Order No.	9012640000
Type	EINSATZPAAR PZ 16E
GTIN (EAN)	4008190114831
Qty.	1 pc(s).

EINSATZPAAR PZ 16E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	12 mm	Depth (inches)	0.472 inch
Height	34 mm	Height (inches)	1.339 inch
Width	28 mm	Width (inches)	1.102 inch
Net weight	39.6 g		

Description of contact

Conductor cross-section, max. AWG	6	Conductor cross-section, min. AWG	10
Crimping range, max.	16 mm ²		

tool data crimping

Crimping type/profile	Indent crimp
-----------------------	--------------

Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90
ECLASS 13.0	21-04-90-90	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Catalogues	Catalogues in PDF-format
------------	--