

CUTTER 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

Version	Cutting tool for one-hand operation
Order No.	9040560000
Type	CUTTER 35
GTIN (EAN)	4008190464943
Qty.	1 pc(s).

CUTTER 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	40 mm	Depth (inches)	1.575 inch
Height	85 mm	Height (inches)	3.346 inch
Width	290 mm	Width (inches)	11.417 inch
Net weight	599.4 g		

Technical data

Description of article	Front cable cutter up to 35 mm outer diameter	Version	One-hand mechanical
------------------------	---	---------	---------------------

Cutting tools

Aluminium sector cable	4 x 70 SE	Copper cable - flexible, max.	240 mm ²
Copper cable - flexible, max. (kcmil)	500 kcmil	Copper cable - stranded, max.	240 mm ²
Copper cable, max. diameter	35 mm	Copper sector cable	3 x 70 SM
Data / telephone / control cable, max. Ø 35 mm		Stranded aluminium cable, max (mm ²)	240 mm ²
Stranded aluminium cable, max. (kcmil)	500 kcmil	Stranded aluminium cable, max. diameter	35 mm

Classifications

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 9.0	21-04-47-01
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-47-01
ECLASS 11.0	21-04-47-01	ECLASS 12.0	21-04-47-01
ECLASS 13.0	21-04-47-01	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

Catalogues	Catalogues in PDF-format
------------	--