

UNIVERSAL CUTTER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

When working with live voltages, you must follow special guidelines and use special tools - tools which have been specially produced and tested for this purpose.

Weidmüller offers a complete line of pliers which comply with national and international testing standards.

All pliers are produced and tested according to DIN EN 60900.

The pliers are ergonomically designed to fit to the hand form, and thus feature an improved hand position. The fingers are not pressed together - this results in less fatigue during operation.

General ordering data

Version	Diagonal-cutting pliers
Order No.	9041470000
Type	UNIVERSAL CUTTER
GTIN (EAN)	4008190397777
Qty.	1 pc(s).

UNIVERSAL CUTTER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	160 mm	Width (inches)	6.299 inch
Net weight	218 g		

Technical data

Version	One-hand mechanical
---------	---------------------

Pliers

Conductor diameter, max. (H)	2.3 mm	Conductor diameter, max. (MH)	3 mm
Cutter hardness	62 HRC	Protective insulation, 1000 V	No
Total length	160 mm		

Classifications

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 9.0	21-04-47-01
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-47-01
ECLASS 11.0	21-04-47-01	ECLASS 12.0	21-04-47-01
ECLASS 13.0	21-04-47-01	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1

Downloads

Catalogues	Catalogues in PDF-format
------------	--