

WK S 0,8X4,0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Interchangeable bits for torque screwdriver**

Drive output acc. to DIN 5264, ISO 2380/1

General ordering data

Version	Screwdriver insert
Order No.	9918550000
Type	WK S 0,8X4,0
GTIN (EAN)	4032248388912
Qty.	1 pc(s).

WK S 0,8X4,0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	4 mm	Depth (inches)	0.157 inch
Height	4 mm	Height (inches)	0.157 inch
Width	175 mm	Width (inches)	6.89 inch
Net weight	25 g		

Technical data

Description of article	Interchangeable bit for slotted screws, size 0.8x4
------------------------	---

Screwing tools

Blade length	175 mm	Blade thickness (A)	0.8 mm
Blade width (B)	4 mm	Form	Slotted
Torque setting, max.	2.5 Nm		

Classifications

ETIM 6.0	EC002116	ETIM 7.0	EC002116
ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 9.1	21-04-04-90
ECLASS 10.0	21-04-04-90	ECLASS 11.0	21-04-42-04
ECLASS 12.0	21-04-42-04	ECLASS 13.0	21-04-42-04
ECLASS 14.0	21-04-42-04	ECLASS 15.0	21-04-42-04

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1

Downloads

Catalogues	Catalogues in PDF-format
Brochures	