



Representative Image

Catalog No. 040-5352

Description: 1/2IN 90D INSL LT CONN IRON W/DURA

UPC No 786210837970

Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors

Liquidtight Connector, Insulated Conduit Joint, 1/2 Inch Flexible, Metal Conduit Connector, 90 Degree Angle, UL Listed Liquidtight, UL Listed As Grounding Means, Under NEC 351-9, Duraplated, 25 Pieces

Descriptors

Category	Liquid tight connectors
Special Features	Dura-Plate Finish

Specifications

Material	Malleable Iron - Insulated
----------	----------------------------

Classifications

Brand Name	T&B Liquidtight Fittings
Standard	CSA, UL

Dimensions

Size	1/2 Inch
------	----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM Classification

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4484	441202	N/A	2206188	N/A