



Catalog No. 5355-8PT

Description: 1-1/4IN 90D LT INSUL CONN STL

UPC No 786210264196

Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors

1-1/4 Inch Liquidtight, Flexible Metal Conduit Connector, 90 Degree Angle, Insulated, UL Listed Liquidtight, UL Listed Grounding Means Under NEC 351-9, In Wet Locations Us #5265 Sealing Ring Between Box and Fitting for Ko Applications, Pack of 50

Descriptors

Category	Liquid tight connectors
----------	-------------------------

Classifications

Brand Name	T&B Liquidtight Fittings
Standard	UL Listed

Dimensions

Size	1-1/4 Inch
------	------------

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	Other
One-piece	N
Material housing	Steel

—
by ABB