



Representative Image

Catalog No. 5523

Description: 1.5 INCH T&B INSUL EMT COMPR CONN

UPC No 786210055237

Home > Cable Protection Systems > T&B Rigid Fittings > Electrical metallic tubing EMT connectors

1-1/2 Inch Insulated Compression Connector, Steel Electro Zinc Plated, Insulator Thermoplastic for Use with EMT Conduit

Descriptors

| | |
|------------------|---|
| Category | Electrical metallic tubing EMT connectors |
| Special Features | Rugged All Steel Construction |
| Application | To Connect and Effectively Bond Electrical Metallic Tubing to a Box or an Enclosure |

Specifications

| | |
|----------|---------------------|
| Material | Steel |
| Finish | Electro Zinc Plated |

Classifications

| | |
|------------|--------------------|
| Brand Name | T&B Rigid Fittings |
| Standard | UL E16592, CSA |

Dimensions

| | |
|------|------------|
| Size | 1-1/2 Inch |
|------|------------|

Compliance and Certifications

| | |
|-------|-----------------------------|
| RoHS | RoHS3 Compliant |
| REACH | REACH 240 Compliant |
| TSCA | TSCA Section 6(h) Compliant |

| | |
|---|--|
| ETIM | EC001180 Screw connection for protective metallic hose |
| Nominal size in inch | 1 1/2 inch |
| Model | Straight |
| Revolving thread | N |
| Construction type | External thread |
| Connection type screw connection to housing | Thread |
| Thread type | NPT |

by ABB

| | |
|--------------------|--|
| ETIM | EC001180 Screw connection for protective metallic hose |
| One-piece | N |
| Material housing | Steel |
| Surface protection | Other |