

Stainless steel conduit, fittings and accessories

Stainless steel pipe straps



Support and securely fasten rigid, IMC and EMT conduit.

- Type 303 stainless steel
- Higher degree of corrosion resistance than traditional zinc-plated or hot-dipped galvanized straps
- One- and two-hole straps for EMT sizes ½" through 2"
- One- and two-hole straps for rigid and IMC sizes ½" through 4"

Type 304 stainless steel pipe straps

Cat. no.	Trade size (in.)	Wt. per 100	Hole dia. (in.)	Std. pkg.
One-hole EMT straps				
TS101-SS	½	2.21	¼	25
TS102-SS	¾	2.49	¼	25
TS103-SS	1	3.31	¼	25
TS104-SS	1¼	3.64	11/16	10
TS105-SS	1½	3.87	11/16	5
TS106-SS	2	4.03	11/16	5
One-hole rigid/IMC straps				
HS100-SS	¾	2.00	9/32	20
HS101-SS	½	2.21	9/32	20
HS102-SS	¾	2.49	9/32	20
HS103-SS	1	3.48	9/32	20
HS104-SS	1¼	3.76	11/32	10
HS105-SS	1½	18.22	13/32	10
HS106-SS	2	19.69	13/32	5
HS107-SS	2½	67.21	15/32	5
HS108-SS	3	76.45	17/32	5
HS110-SS	4	80.18	17/32	5

Cat. no.	Trade size (in.)	Wt. per 100	Hole dia. (in.)	Std. pkg.
Two-hole EMT straps				
TS901-SS	½	2.21	¼	25
TS902-SS	¾	3.31	¼	25
TS903-SS	1	3.87	¼	25
TS904-SS	1¼	7.54	11/16	10
TS905-SS	1½	12.21	11/16	5
TS906-SS	2	18.23	11/16	5
Two-hole rigid/IMC straps				
HS901-SS	½	2.49	9/32	20
HS902-SS	¾	3.64	9/32	20
HS903-SS	1	4.15	9/32	20
HS904-SS	1¼	8.17	11/32	10
HS905-SS	1½	17.50	13/32	10
HS906-SS	2	21.37	13/32	5
HS907-SS	2½	21.54	15/32	5
HS908-SS	3	25.72	17/32	5
HS909-SS	3½	27.27	17/32	5
HS910-SS	4	31.70	17/32	5

Stainless steel conduit, fittings and accessories

Type 316 stainless steel pipe straps



Support and securely fasten rigid conduit.

- Type 316 stainless steel
- Higher degree of corrosion resistance than traditional zinc-plated or hot-dipped galvanized straps
- One- and two-hole straps for rigid and IMC sizes ½" through 4"

Type 316 stainless steel pipe straps

Cat. no.	Trade size (in.)	Hole dia. (in.)	Wt. per 100 (lbs.)
One-hole rigid/IMC stainless steel 316 straps			
HS101SST	½	0.25	4
HS102SST	¾	0.25	5
HS103SST	1	0.31	8
HS104SST	1¼	0.38	12
HS105SST	1½	0.44	15
HS106SST	2	0.56	24
HS107SST	2½	0.56	43
HS108SST	3	0.56	47
HS110SST	4	0.56	72

Cat. no.	Trade size (in.)	Hole dia. (in.)	Wt. per 100 (lbs.)
Two-hole rigid/IMC stainless steel 316 straps			
HS901SST	½	0.19	2
HS902SST	¾	0.19	3
HS903SST	1	0.25	4
HS904SST	1¼	0.25	6
HS905SST	1½	0.25	9
HS906SST	2	0.38	11
HS907SST	2½	0.38	16
HS908SST	3	0.38	20
HS910SST	4	0.44	29