

Catalog No. TY5232MXR-RW

Description: TY232MX FOR RAILWAY SP

UPC No 5415022243505

[Home](#) > [Wire & Cable Management](#) > [Ty-Rap](#) > [Cable ties](#)

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant for Exterior Applications, Length of 203.2mm (8.0 Inches), Width of 2.54mm (0.10 Inches), Thickness of 1.10mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), 100 Bulk Pack

Representative Image

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb

Classifications

Brand Name	Ty-Rap
------------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC000046 Cable tie
Band width	2.54 mm
Length belt/tape/tie	203.2 mm
Length belt/tape/tie	8 inch
Tie thickness	1.1 mm
Tie thickness	0.043 inch
Min. holding force	80 N
Model	Internal toothed
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated

by ABB

ETIM	EC000046 Cable tie
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N