



Representative Image

Catalog No. TYD10M

Description: CABLE TIE DELTEC .5X10 DOUBLE-LOCK

UPC No 786210980843

Home > Wire & Cable Management > Deltec > Cable ties

Deltec Cable Tie with Double-Locking Head, Black Acetal for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant, Length of 635mm (25 Inches), Width of 12.7mm (0.5 Inch), Thickness of 1.52mm (0.06 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds)

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Acetal (POM)
Color	Black
Lock Mechanism	Double Locking Head
Tensile Strength	250 pounds , 1112 newtons

Classifications

Brand Name	Deltec
------------	--------

Dimensions

Width	0.5 in , 12.7 mm
Length	25 in , 635 mm
Thickness	0.06 in , 1.52 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 233 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	12.7 mm
Length belt/tape/tie	635 mm
Length belt/tape/tie	25 inch
Tie thickness	1.52 mm
Tie thickness	0.06 inch

ETIM	EC000046 Cable tie
Min. holding force	1112 N
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Other
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N