

Solder-in breadboard 240 plated holes

Product Highlights

Immersion Gold Finish
Plated through holes
240 holes in total
0.1" hole grid
15 rows, 16 columns

Specifications

Dimensions:	1.7" x 1.75" x 0.0625"
PCB construction:	FR-4 UL94V-0
PCB operating temperature range:	-40°C to +130°C
PCB reflow maximum temperature:	+260°C
Hole size:	1.0mm (40 mils) diameter
	Holes accept 25 mil square wire wrap posts

