

SBBTH4060-1 *Proto Advantage*

Datasheet revision 1.1

www.Proto-Advantage.com

Large Solder-in breadboard 2400 plated holes

Product Highlights

Immersion Gold Finish
Plated through holes
2400 holes in total
0.1" hole grid
40 rows, 60 columns

Specifications

Dimensions:	6.1" x 4.2" x 0.0625"
PCB construction:	FR-4 UL94V-0
PCB operating temperature range:	-40°C to +130°C
PCB reflow maximum temperature:	+260°C
Hole size:	1.0mm (40 mils) diameter Holes accept 25 mil square wire wrap posts

