

## Sn10/Pb88/Ag2 .031" Solder Wire 1oz Spool (Solid Core) (Tin/Lead/Silver)

### Product Highlights

Leaded Solid Core Solder Wire 10/88/2 Tin/Lead/Silver

### Specifications

Alloy:	Sn10/Pb88/Ag2
Wire diameter:	0.031" (0.8mm)
Flux Core:	No flux core, solid solder wire
Melting Point:	268-290°C (514-554°F)
Packaging:	1 oz spool
Shelf Life:	>60 months

### Recommended Accessory Flux

Recommended to use with Chip Quik® SMD291 flux.

### Storage and Handling

Store in a non-corrosive, dry environment.

