


CORE DIMENSIONS:



A	25.91 [1.020]	+	0.70 [.028]
B	13.06 [.514]	+	0.45 [.018]
C	28.58 [1.125]	+	0.64 [.025]
D	12.95 [.510]	+	0.40 [.016]

IMPEDANCE (Z)			
Frequency	25 MHz	100 MHz	300 MHz
Nominal (REF)	130 Ω	280 Ω	440 Ω
Minimum	- Ω	224 Ω	- Ω

Z vs. FREQUENCY
(REF. ONLY)



AGILENT E4991A Impedance/Material Analyzer
HP 16092A-Test Fixture, REF 3158



NOTES:

- ASSEMBLED PART #: 28A2024-0A2
- CASE COLOR: BLACK.
- CASE FLAMMABILITY RATING: UL94 V-2.
- CASE MATERIAL: Halogen Free Nylon
- COSMETIC SPECIFICATION REFER TO WI-QA-038.

CASE DIMENSIONS:

A	29.00 [1.142]	+	1.00 [.039]
B	13.00 [.512]	+	1.00 [.039]
C	32.50 [1.280]	+	1.00 [.039]
D	29.62 [1.166]	+	1.00 [.039]
E	5.64 [.222]	+	REF.

DIMENSIONS ARE IN mm[INCHES].				This print is the property of Laird Tech. and is loaned in confidence subject to return upon request and with the understanding that no copies shall be made without the written consent of Laird Tech. All rights to design or invention are reserved.			
H	RELAX CORE TOL	10/29/15	Jcai				
G	UPDATE CASE DIMENSIONS REMOVE CORE DIM AND ADD NOTE 5&6	01/13/14	Jcai				
F	UPDATED NOTE 3	09/15/10	JUN	PROJECT/PART NUMBER:			
E	UPDATE COMPANY LOGO ADD NOTES 3&4	01/27/09	JRK	28A2024-0A2			
D	UPDATE 100 MHz MINIMUM VALUE CORRECT CASE DIM "B" TOLERANCE SYMBOL	06/07/07	TMB	DATE: 06/29/04			
C	UPDATE COMPANY LOGO	04/18/07	TMB	SCALE: NTS			
REV	DESCRIPTION	DATE	INT	TOOL # -			
				MATERIAL: FERRITE			