THIS DRAWING IS THE EXCLUSIVE PROPERTY OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.
CONFIDENTIAL
VERTRAULICH

1	2	3	4
recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
	0.8 to 5	30 +0.15	22.2 +0.15





"The IP- protection mentioned in our documents refers to the actuating side of the switch.
The sealing between switch and customer appliance and the testing of the tightness have to be effected by the customer."

Marking
MARQUARDT
1670.
16(4)/250~ T85/55





Code of manufacture: place/year/week

DPST
Neon lamp with Rv for 115-230 V AC
Total travel 4±0.4
Suitable for appliances of class II
Actuating side protected acc. to DIN 40 050, IP 54



Figure	Type	Customer Part No.	Art.No.-PI
-	-	-	1670.5203-XX

Shape and location	Angle ± 2 °	Length				Radii	
	Edge tolerance	0-6	± 0.2		±		± 0.2
		>6-15	± 0.4		±		±
		>15-30	± 0.4		±		±
		>30-70	± 0.6		±		±
			±		±		±
			±		±		±
			±		±		±
			±		±		±

Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
f	137245	2022-02-25	MOHITEN
e	39574	2004-02-09	WJ
d	36501	2003-09-01	VOR
c	32547	2002-08-22	WJ

Sheet 01

Format DIN	Projection	Scale
A4		1:1

All dimensions are in millimetres

System NX V1872

Replacement of Zg.gl.Nr.v.04.06.1997

Ident.	Document number	Index
K	16705203	f

Appliance Switch

MARQUARDT

Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsanmeldungen. Jede Verfuegungsbefugnis, wie Kopier- und Weitergaberecht, bei uns.