

CONFIDENTIAL

VERTRAULICH

THIS DRAWING IS THE EXCLUSIVE PROPERTY OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsanmeldungen. Jede Veruegungsbefugnis, wie Kopier- und Weitergaberecht, bei uns.

1
2
3
4

A
B
C
D
E

Betaetigungskraft $F=9N \pm 3N$
operating force $F=9N \pm 3N$

Flachstecker aeihn./plug in sim.
DIN46244-A 4.8-0.8

Ausschalter 2-polig
fuer Gerate der Klasse II geeignet
DPST
suitable for appliances of class II

G-Konform nach IEC 60335-1:2001 Kap.30
G-matching IEC 60335-1:2001 clause 30

Aufschrift
Marking

168..
16(41)/250 ~
12(12)/250 ~
10(8)/250 ~ 5E4
 05 T125
R97

Aufschriftbeschreibung
marking description
R97= 12A 125-250 VAC
1/2HP 125-250 VAC

Herstellort/-jahr/-woche
Code of manufacture: place/year/week
on box: Customer Part No. see variant table

Schaltstellung/ operating position	h
AUS/off	24.0
EIN/on	20.95
Block/block	19.7

-	-	6.630-437.0	1689.1802-XX
Figure	Type	Customer Part No.	Art.No.-PI
Shape and location	Angle $\pm 2^\circ$	Sheet 01	
	Edge tolerance	Ident. K	Document number 16891802
	Length	Scale 1:1	Index c
	Radii	appliance switch	
All dimensions are in millimetres			
c	146818	2023-08-14	ABASSIAI
b	64355	2009-07-20	MUT
a	52247	2007-04-23	HHE
	51507	2007-04-05	MUT
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
System NX V1899		Replacement of V07011021	
		MARQUARDT	