





A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness 0.75 to 1.25 1.25 to 2 2 to 3	length of cut-out 19.2 -0.1 19.4 -0.1 19.8 -0.1	width of cut-out 21.9 +0.1 21.9 +0.1 21.9 +0.1
B				
C				
D				
E	Marking  1802.  6(4)/250 ~ 5E4 10(4)/250 ~ 5/50A 250V ~ T100/55 6A 125-250V AC 1/4HP 125V AC 1/2HP 250V AC R30  DPST suitable for appliances of class II  Code of manufacture: place/year/month			

-	-	-	1802.1102-XX
Figure	Type	Customer Part No.	Art.No.-PI
Shape and location	Angle $\pm 2^\circ$	Sheet 01	
	Edge tolerance	Ident. K	Document number 18021102
	Length	Projection	Index j
	Radii	Scale 1:1	
j	137845	2023-06-06	MUT
i	61657	2009-01-20	VOR
h	46880	2006-04-04	vor
g	37630	2003-09-16	VOR
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
All dimensions are in millimetres		System NX V1899	Replacement of
		Zg.gl.Nr.v.21.07.1997	
 MARQUARDT			